

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640160042](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ServiceGrade Hand Crimp Tool - Ratchet

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	ServiceGrade crimp hand tools are low cost ratcheting hand tools used in field repair for a limited number of terminations. If a high quality tool is required or a higher volume of terminations required, please purchase the corresponding PremiumGrade crimp hand tool. A ServiceGrade crimp tool may or may not have a terminal locator and in some case may need the locator removed to operate properly. Type: SERV GRADE
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ServiceGrade
Tool Type	Hand Crimp Tool
UPC	822348487769
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number 5771

Reference - Drawing Numbers

Application Tooling Documents [ATS-640160042-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129](#) Series

Use With

Fully insulated Quick Disconnect for 14-22 AWG and Step Down Butt Splices for 10-12 to 14-16 AWG and 14-16 to 18-22 AWG. The PremiumGrade Hand Tool for OEM Customers would be Part Number 640014500

Application Tooling Description

FAQ Product #

Perma-Seal Male [191640015](#)

Quick Disconnect Tab for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm, Bag

Perma-Seal Female [191640017](#)

Quick Disconnect Receptacle for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm

Perma-Seal Male [191640048](#)

Quick Disconnect Tab for 14-16 AWG

Wire, Tab Size 6.35
x 0.81mm, Bag
Perma-Seal Female [191640050](#)
Quick Disconnect
Receptacle for 14-16
AWG Wire, Tab Size
6.35 x 0.81mm

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64016-0042](#)