

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640160044](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ServiceGrade Hand Crimp Tool - Ratchet

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	ServiceGrade crimp hand tools are low cost ratcheting hand tools used in field repair for a limited number of terminations. If a high quality tool is required or a higher volume of terminations required, please purchase the corresponding PremiumGrade crimp hand tool. A ServiceGrade crimp tool may or may not have a terminal locator and in some case may need the locator removed to operate properly. Type: SERV GRADE
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ServiceGrade
Tool Type	Hand Crimp Tool
UPC	822350644150
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)

ATS-640160044-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Terminates RJ-22 (4 position), RJ-11 (6 position) and RJ-45 (8 position) Modular Plugs. The PremiumGrade Hand Tool for OEM Customers would be Part Number [622020500](#)

Application Tooling

FAQ

Description	Product #
-------------	-----------

Modular Plug, Category 6, Long Body, Unshielded, 8/8	449150001
--	---------------------------

Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief	449150011
---	---------------------------

Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief	449150012
---	---------------------------

Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief	449150021
---	---------------------------

Modular Plug, Category 6, Long	449150021
--------------------------------	---------------------------

Modular Plug, Category 6, Long	449150021
--------------------------------	---------------------------

Modular Plug, Category 6, Long	449150021
--------------------------------	---------------------------

Modular Plug, Category 6, Long	449150021
--------------------------------	---------------------------

Body, Shielded, 8/8,
with Strain Relief
Modular Plug, 449150022
Category 6, Long
Body, Shielded, 8/8,
with Strain Relief

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64016-0044](#)