

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0797582025](#)  
**Status:** **Active**  
**Overview:** Off-the-Shelf Pre-Crimped Leads  
**Description:** Pre-Crimped Lead .062" Male-to-.062" Male, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |  |
|------------------------|--|
| Product Family         | Cable Assemblies                       |
| Series                 | <a href="#">79758</a>                  |
| Assembly Configuration | Pre-crimped Lead Only                  |
| Connector to Connector | .062" Crimp Terminals                  |
| Overview               | <u>Off-the-Shelf Pre-Crimped Leads</u> |
| Product Name           | Standard .062"                         |
| UPC                    | 889056822763                           |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 150.00mm             |
| Circuits (Loaded)              | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Male-Male            |
| Material - Metal               | Brass                |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 1.647/g              |
| Packaging Type                 | Bag                  |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Size AWG                  | 22                   |
| Wire/Cable Type                | UL 1061              |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2012341213-000 |
|---------------|----------------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[79758 Series](#)

**Use With**

[1625](#) , [2004](#) , [1772](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79758-2025](#)