

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013473](#)
Status: **Active**
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», Black, with IP66 - Ribbon Cable Gland, Grey, Cable Size 3.80-9.00mm x 40.00-47.00mm, High Construction

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Cable Gland Type IP66 - Ribbon Cable
 Component Size 24B «104X27»
 Component Type Double Lever Hood
 Overview [GWconnect® Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type STD
 UPC 887191893228

Physical

Entry Location Top
 Flammability UL 94V-0
 Gland Color Grey RAL 7037
 Hood Color Black RAL 9005
 Lock to Mating Part Yes
 Material - Cable Gland Polyamide
 Material - Gasket Silicone
 Material - Hood Die-cast Aluminum
 Material - Peg Stainless Steel
 Number of Pegs 4
 Packaging Type Bag
 Ribbon Cable Size 3.80-9.00mm X 40.00-47.00mm
 Temperature Range - Operating -40°C to +100°C
 Waterproof / Dustproof Yes
 Waterproof / Dustproof Type IP66, IP69

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7824.5372.1



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

| | |
|-----------------|--------------|
| China ROHS | Not Reviewed |
| ELV | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

[93601](#) Series

Use With

Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K,S-M, and S-EHV Inserts and Ribbon Cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3473](#)