

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936013526](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect EMC - Electromagnetic Compatibility, Double Lever Surface Mount Housing, Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», M25 Thread

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                  |   |
|------------------|---|
| Product Family   | Industrial Connectors / Enclosures                      |
| Series           | <a href="#">93601</a>                                   |
| Component Size   | 24B «104X27»  |
| Component Type   | Double Lever SMT Housing                                |
| IP Rating        | IP66, IP69  |
| Overview         | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a>   |
| Product Category | Heavy Duty Connectors                                   |
| Product Name     | GWconnect   |
| Standard         | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type             | EMC   |
| UPC              | 887191843223  |

**Physical**


|                     |                  |
|---------------------|------------------|
| Lock to Mating Part | Yes              |
| Material - Gasket   | NBR              |
| Material - Housing  | Aluminum         |
| Material - Lever    | Galvanized Steel |
| Mounting Style      | Surface Mount    |
| Net Weight          | 360.000/g        |
| Number of Levers    | 2                |
| Packaging Type      | Bag              |
| Thread Size         | M25              |
| Thread Type         | (M) Metric       |

**Electrical**

|                   |      |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

**Material Info**

|                    |             |
|--------------------|-------------|
| Engineering Number | 7824.6376.4 |
|--------------------|-------------|



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 24B «104x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-HSB, S-K and S-M Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3526](#)