

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0982680728](#)  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 1.25mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 5 Circuits

**Documents:**

|  |  |
|--|--|
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Product Specification PS-98268-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**General**

|                         |   |
|-------------------------|---|
| Product Family          | Cable   |
| Series                  | 98268   |
| Comments                | Contacts on opposite sides, Type D  |
| Crimp Quality Equipment | Yes   |
| Overview                | <a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a> |
| Product Name            | Premo-Flex FFC Jumper   |
| UPC                     | 800756951812  |

**Physical**

|                               |                   |
|-------------------------------|-------------------|
| Cable Length                  | 102.00mm          |
| Circuits (Loaded)             | 5                 |
| Contact Layout Type           | D (opposite side) |
| Material - Plating Mating     | Tin               |
| Packaging Type                | Bag               |
| Pitch - Mating Interface      | 1.25mm            |
| Temperature Range - Operating | -40° to +105°C    |
| Wire Size AWG                 | N/A               |
| Wire/Cable Type               | Flat Flex Cable   |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.4A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-98268-001-001 |
| Sales Drawing         | SD-98268-001-001 |



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[98268 Series](#)

**Mates With**

<a href="http://www.molex.com/product/ffc">Molex FFC – FPC connector</a>. Be sure to match like plating.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98268-0728](#)