

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988161111](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC Unsealed Female Housing, 10 Circuits, Dual Row, Black, Version 1 without Ear

Documents:

[3D Model](#) [Packaging Specification PK-98816-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-98816-001-001 \(PDF\)](#)

Application tooling part link

Application Tooling Part Link 63813-7500

General

Product Family Crimp Housings
 Series [98816](#)
 Application Power, Wire-to-Wire
 Comments Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
 Overview [NSCC - New Standard Casing Contact](#)
 Product Name NSCC
 UPC 822348816293

Physical

Circuits (maximum) 10
 Circuits Detail 10x1.5mm female terminals
 Color - Resin Black
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 4.700/g
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.33mm, 6.00mm
 Polarized to Mating Part Yes
 Ports 1
 Temperature Range - Operating -40° to +85°C

Electrical

Current - Maximum per Contact 10.0A

Solder Process Data

Lead-free Process Capability N/A

Material Info

Engineering Number 18101EV10M1

Reference - Drawing Numbers

Application Specification AS-98816-001-001
 Packaging Specification PK-98816-001-001
 Sales Drawing SD-98816-005, SD-98816-006



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[98816 Series](#)

Mates With

[988231011](#) (Male Receptacle Housing)

Use With

[98897](#) Female Terminal NSCC or FCI
 Female Terminal 1.5 Sicma 3

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for NSCC Female Housing [638137500](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98816-1111](#)