

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0988241010**  
**Status:** **Active**  
**Overview:** NSCC - New Standard Casing Contact  
**Description:** NSCC Pin Connector, Unsealed, 2.8mm, 5.00mm Pitch, 2 Circuits, White

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 988210001-PS-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-98821-001-001 (PDF)</a>
<a href="#">Product Specification PS-98821-001-001 (PDF)</a>	<a href="#">Packaging Specification PK-98824-001 (PDF)</a>
<a href="#">Application Specification 988210001-AS-CH-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Application tooling part link**

Application Tooling Part Link 63813-3800

**General**

Product Family	Crimp Housings
Series	98824
Application	Power, Wire-to-Wire
Overview	<a href="#">NSCC - New Standard Casing Contact</a>
Product Name	NSCC
UPC	822348760411

**Physical**

Circuits (maximum)	2
Circuits Detail	2x2.80mm pins
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.660/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	5.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +85°C

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Engineering Number 08219EV2F9

**Reference - Drawing Numbers**

Application Specification	988210001-AS-CH-001, 988210001-PS-CH-001, AS-98821-001-001
Packaging Specification	PK-98824-001
Product Specification	PS-98821-001-001
Sales Drawing	SD-98824-002



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -ED/01/2018 (15 January 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

98824 Series

**Mates With**

98824 NSCC 3.33mm Pitch Female Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extractor Tool for Unsealed Receptacle Connectors	<a href="#">638133800</a>

This document was generated on 03/01/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98824-1010](#)