

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300640065](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower D-Size (1 3/8"-M35) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 10 AWG, PVC Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family Industrial Cordsets  
 Series [130064](#)  
 Connector End A BradPower D-Size (1 3/8"-M35)  
 Connector End B BradPower D-Size (1 3/8"-M35)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [BradPower Cordsets and Receptacles](#)  
 Product Name BradPower D-Size  
 Protocol EtherNet  
 Region Europe  
 Type Double Ended  
 UPC 78678882698

**Physical**

Cable Diameter 17.78mm (.700")  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Gray  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body TPE  
 Material - Coupling Nut Anodized Aluminum  
 Material - Plating Mating Gold  
 Net Weight 254.000/g  
 Orientation Straight to Straight  
 Poles 3  
 Temperature Range - Operating -20°C to +90°C  
 Wire Size AWG 10  
 Wire/Cable Type ST00W, TC-ER Direct Burial

**Electrical**


Current - Maximum per Contact 32.0A  
 Voltage - Maximum 600V AC/DC

**Material Info**

Engineering Number CC3030A48M020

**Reference - Drawing Numbers**

Sales Drawing SD-130064-065-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130064 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300640065](#)