

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300830781](#)  
**Status:** **Active**  
**Overview:** Reels - Woodhead  
**Description:** Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length with 20A Connector and Ball Stop

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921  
 UL E22769

**General**

Product Family Electric Reels  
 Series [130083](#)  
 Cable Length N/A  
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.  
 Depth 0.34m (13.50")  
 Duty Industrial  
 Enclosure Rating NEMA 4  
 Height 0.37m (14.50")  
 NEMA Configuration NEMA 5-20  
 Overview [Reels - Woodhead](#)  
 Product Name POW-R-MITE  
 Type Cable Reel  
 UPC 78678834666  
 Width 244.35mm (9.620")

**Physical**

Cable Movement Ratchet Lock  
 Cord Length 15.24m (50.0')  
 Drum Lock Ratchet  
 Guide Arm 5° increments over 270° Arc  
 Material - Coating Powder Coating  
 Material - Housing Cast Aluminum  
 Mounting Style Rigid  
 Net Weight 22679.600/g  
 Number of Conductors 3  
 Number of Receptacles 1  
 Packaging Type Carton  
 Primary Cord/Cable Entry 1" NPT  
 Retraction Weight 1.8kg (4.0 lb)  
 Wire Size AWG 12

**Electrical**

Bulb Included N/A  
 Cord Type 12/3 SOW  
 Current - Maximum per Contact 18.0A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 120V

**Material Info**

Engineering Number 92433-1533



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[130083 Series](#)

This document was generated on 07/29/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300830781](#)