


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1510350006](#)
Status: **Active**
Overview: [EXTreme Guardian System](#)
Description: 11.00mm Pitch EXTreme Guardian Power Right-Angle Plug PCB Header, 2.36mm PCB Thickness, Gold Plated, 6 Circuits

Documents:

3D Model	Packaging Specification PK-151035-0001-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-151035-0006 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-151053-0000-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	151035
Application	Power, Wire-to-Board
Overview	EXTreme Guardian System
Product Name	EXTreme Guardian
UPC	889056053525

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	48.122/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.86mm
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Pitch - Mating Interface	11.00mm
Plating min - Mating	0.076µm
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	80.0A
Voltage - Maximum	600V AC/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[151035 Series](#)

Mates With

[EXTreme Guardian Receptacle Housing
151034](#)

Reference - Drawing Numbers

Packaging Specification

PK-151035-0001-001

Product Specification

PS-151053-0000-001

Sales Drawing

SD-151035-0001-001

Symbol/Footprint Data

SYM-151035-0006

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151035-0006](#)