

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1510530003](#)
Status: **Active**
Overview: [EXTreme Guardian System](#)
Description: 11.00mm Pitch EXTreme Guardian Power Vertical Plug PCB Header, 2.30mm PCB Thickness, Gold Plated, 3 Circuits

Documents:

3D Model	Application Specification 1510350000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification PK-151053-0001-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-151053-0003-001 (PDF)
Product Specification PS-151053-0000-001 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

Application tooling part link

Application Tooling Part Link 200199-1500

General

Product Family	PCB Headers
Series	151053
Application	Power, Wire-to-Board
Overview	EXTreme Guardian System
Product Name	EXTreme Guardian
UPC	889056571715

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	18.531/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.83mm
PCB Locator	No
PCB Thickness - Recommended	2.30mm
Packaging Type	Tray
Pitch - Mating Interface	11.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	80.0A
Voltage - Maximum	600V AC/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[151053 Series](#)

Mates With

[EXTreme Guardian Receptacle Housing
151034](#)

Material Info

Reference - Drawing Numbers

Application Specification	1510350000-AS-000
Packaging Specification	PK-151053-0001-001
Product Specification	PS-151053-0000-001
Sales Drawing	SD-151053-0001-001
Symbol/Footprint Data	SYM-151053-0003-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151053-0003](#)