

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552300209](#)  
**Status:** **Active**  
**Overview:** Flamar Standard and Custom Cables for Industrial Automation  
**Description:** Flamar Control Cable, PUR Jacket, Unshielded, 25 Circuits, 1.00mm<sup>2</sup> with Green-Yellow Ground / 18 AWG with Green-Yellow Ground, 16.00mm (.236") Diameter, 250.0m (820.21') Length, Gray

**Documents:**

[Product Specification 1552300001-P1E \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155230</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Signal and Control
UPC	889056448321

**Physical**

Bending Radius - Minimum	> 7.5xOD
Cable Length	250.0m
Circuits (Loaded)	25
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	PUR
Net Weight	0.010/g
Outer Jacket Diameter	16.00mm
Packaging Type	Reel
Temperature Range - Operating	-40° to +80°C
Wire Size AWG	18
Wire Size mm <sup>2</sup>	1.00
Wire/Cable Type	UL AWM 21223 / CSA

**Electrical**


Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V

**Material Info**

Engineering Number	1X250M
--------------------	--------

**Reference - Drawing Numbers**

Product Specification	1552300001-P1E
-----------------------	----------------



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155230 Series](#)

**Use With**

DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#)  
 <br>Micro-Change (M12) [120071](#) <br>Ultra-Lock (M12) [120085](#) <br>GWconnect Heavy Duty Connectors [93601](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155230-0209](#)