

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552209006](#)

Status: **Active**

Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)

Description: Flamar Distribution Box Cable, WSOR Jacket, Unshielded, 7 Circuits, 3x(0.75mm²) with Green-Yellow Ground + 4x(0.34mm²) / 3x(19 AWG) with Green-Yellow Ground + 4x(22 AWG), 7.80mm (.307") Diameter, 1000.0m (3280.83') Length, Grey

Documents:

[Product Specification 1552209001-P1E \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 155220 |
| Crimp Quality Equipment | Yes |
| Geographic Area | Global |
| Overview | Flamar Standard and Custom Cables for Industrial Automation |
| Product Name | Flamar, Signal and Control |
| UPC | 889056463249 |

Physical

| | |
|-------------------------------|--------------------|
| Bending Radius - Minimum | > 10xOD |
| Cable Length | 1000.0m |
| Circuits (Loaded) | 7 (3+4) |
| Color - Cable Jacket | Gray |
| Insulation | TPE |
| Material - Outer Jacket | WSOR |
| Net Weight | 0.010/g |
| Outer Jacket Diameter | 7.80mm |
| Packaging Type | Reel |
| Temperature Range - Operating | -25° to +80°C |
| Wire Size AWG | 19, 22 |
| Wire Size mm ² | 0.34, 0.75 |
| Wire/Cable Type | UL AWM 21215 / CSA |

Electrical


| | |
|-------------------------------|---------------|
| Current - Maximum per Contact | Contact Molex |
| Voltage - Maximum | 600V |

Material Info

| | |
|--------------------|---------|
| Engineering Number | 1X1000M |
|--------------------|---------|

Reference - Drawing Numbers

| | |
|-----------------------|----------------|
| Product Specification | 1552209001-P1E |
|-----------------------|----------------|



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[155220](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-9006](#)