

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2037023000](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** FineAdjust Applicator for Nano-Fit Wire-to-Wire Plug Terminals, 20-22 AWG UL1061 and 22 AWG UL1007 Wires

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                                |   |
|--------------------------------|---|
| Product Family                 | Application Tooling   |
| Series                         | <a href="#">207127</a>  |
| Comments                       | See Tooling Specification (PDF) Above   |
| Function                       | Crimp   |
| Geographic Area                | Global  |
| Level of Automation            | Automatic, Semi-Automatic   |
| More Detailed Tech Information | <a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>  |
| Overview                       | <a href="#">Application Tooling</a>   |
| Product Name                   | FineAdjust, Nano-Fit  |
| Tool Type                      | Applicator  |
| UPC                            | 193264302666  |
| Warranty Disclaimer            | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

**Physical**

Net Weight 5000.000/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents [2037023000-000](#)



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207127](#) Series

**Application Tooling** | [FAQ](#)

| Description  | Product #                  |
|--|----------------------------|
| Nano-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 20-22 AWG             | <a href="#">2014472200</a> |
| Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, 20-22 AWG             | <a href="#">2014472300</a> |
| Nano-Fit Crimp Terminal, Male, 2.54µm Matte Tin Plating, Lubricated, 20-22 AWG | <a href="#">2014472400</a> |
| Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, Lubricated, 20-22 AWG | <a href="#">2014472600</a> |

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[203702-3000](#)