

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2045320201](#)

Status: **Active**

Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)

Description: Micro-Lock Plus Receptacle Housing, 1.25mm Pitch, Single Row, with Positive Lock, 2 Circuits, Low-Halogen, Black

Documents:

3D Model	Product Specification 2045321000-PS-001 (PDF)
3D Model (PDF)	Product Specification 2045321001-PS-000 (PDF)
Drawing (PDF)	Application Specification AS-505565-001-001 (PDF)
Product Specification 2045320000-PS-000 (PDF)	Packaging Specification 2045329200-200 (PDF)
Product Specification 2045320000-PS-001 (PDF)	Datasheet (PDF)
Product Specification 2045320001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	204532
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
UPC	191128418232

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	61.613/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-505565-001-001
Packaging Specification	2045329200-200
Product Specification	2045320000-PS-000, 2045320000-PS-001, 2045320001-PS-000, 2045321000-PS-001, 2045321001-PS-000
Sales Drawing	2045320000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204532](#) Series

Mates With

Micro-Lock Plus Header [205957](#)

Use With

Micro-Lock Plus Terminal [505431](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[204532-0201](#)