

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2074580006](#)
Status: **Active**
Overview: [L1NK Connector System](#)
Description: L1NK 396 Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Black

Documents:

3D Model	Product Specification 2074580000-PS-SK-000 (PDF)
3D Model (PDF)	Product Specification 2074580000-TS-000 (PDF)
Drawing (PDF)	Packaging Specification 2074580000-PK-000 (PDF)
Product Specification 2074580000-PS-CH-000 (PDF)	Packaging Specification 2074580000-PS-000 (PDF)
Product Specification 2074580000-PS-ES-000 (PDF)	Datasheet (PDF)
Product Specification 2074580000-PS-JP-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	207458
Application	Power, Wire-to-Board
Overview	L1NK Connector System
Product Name	L1NK 396
UPC	191130115600

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.090/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2074580000-PK-000, 2074580000-PS-000
Product Specification	2074580000-PS-CH-000, 2074580000-PS-ES-000, 2074580000-PS-JP-000, 2074580000-PS-SK-000, 2074580000-TS-000
Sales Drawing	2074580000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207458](#) Series

Mates With

L1NK 396 Headers [207478](#) , [207479](#)

Use With

MarKK Crimp Terminal [455703000](#) ,
[455703002](#) , [455703050](#) , [455703052](#) .
L1NK TPA Retainer [207459](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[207458-0006](#)