

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200868393](#)  
**Status:** **Active**  
**Overview:** [Brad Nano-Change \(M8\) Products](#)  
**Description:** Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Male (90°) to Pigtail, 0.25mm<sup>2</sup> Black PUR LSOH Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120086](#)  
 Connector End A Nano-Change (M8)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Nano-Change \(M8\) Products](#)  
 Product Name Nano-Change (M8)  
 Protocol N/A  
 Region Europe  
 Type Single Ended  
 UPC 78172532887

**Physical**

Cable Diameter 4.10mm (.161")  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Black  
 Coupling Style Threaded  
 Gender Male-Pigtail  
 Keyway A-coded  
 LED Indicator No  
 Material - Cable Jacket PUR  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Material - Plating Mating Gold  
 Net Weight 60.600/g  
 Orientation 90° to Pigtail  
 Poles 3  
 Temperature Range - Operating -25° to +80°C  
 Wire Size AWG 24  
 Wire/Cable Type UL 21198

**Electrical**


Current - Maximum per Contact 3.0A  
 Voltage - Maximum 60V AC / 75V DC

**Material Info**

Engineering Number 403007H08M020

**Reference - Drawing Numbers**

Sales Drawing 1200868083-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)4578-DC (25 June 2020)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[120086 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200868393](#)