

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2035113112](#)  
**Status:** **Active**  
**Overview:** [MX64 Sealed Connectors](#)  
**Description:** 2.54mm MX64 Sealed Single Row Crimp Housing for LED Light Modules, MX64 Terminal, Black, 3 Circuits, Key A, without CPA Lock, Terminal Position 2 Plugged

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 2035110001-AS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">203511</a>
Application	Power, Wire-to-Board
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership</a>
Overview	<a href="#">MX64 Sealed Connectors</a>
Polarization	A
Product Name	MX64
UPC	191128254076

**Physical**


Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.991/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

**Material Info**

Engineering Number	CVP-2035113112
--------------------	----------------

**Reference - Drawing Numbers**

Application Specification	2035110001-AS-000
Sales Drawing	2035110001-000



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[203511 Series](#)

**Mates With**

LED Modules, Other USCAR Interfaces

**Use With**

Molex MX64 Terminals [33468](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[203511-3112](#)