

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2065232162](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Receptacle, Dual Row, UL94-HB, with CPA, 16 Circuits, Polarization Option B, Gray

Documents:

[3D Model](#) [Product Specification 2065230000-PS-000 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-31301-538-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Housings](#)
Series [206523](#)
Application [Automotive, Power, Wire-to-Board](#)
Overview [Mini50 Connection Systems](#)
Polarization [B](#)
Product Name [Mini50](#)
UPC [191130110087](#)


Physical

Circuits (maximum) [16](#)
Color - Resin [Gray](#)
Gender [Receptacle](#)
Glow-Wire Capable [No](#)
Keying to Mating Part [Yes](#)
Lock to Mating Part [Yes](#)
Material - Resin [PBT](#)
Net Weight [1.860/g](#)
Number of Rows [2](#)
Packaging Type [Bag](#)
Panel Mount [No](#)
Pitch - Mating Interface [2.00mm](#)
Pitch - Termination Interface [2.00mm](#)
Polarized to Mating Part [Yes](#)
Stackable [No](#)
Temperature Range - Operating [-40° to +100°C](#)

Material Info

Reference - Drawing Numbers

Packaging Specification [PK-31301-538-001](#)
Product Specification [2065230000-PS-000](#)
Sales Drawing [2065230000-000](#)



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[206523](#) Series

Mates With

Mini50 Surface Mount Header [348978161](#)
, [348979161](#)
 Mini50 Vertical Through-
Hole Header [348250161](#) , [348259161](#)

Mini50 Right-Angle Through-Hole Header
[348260161](#) , [348269161](#)

Use With

CTX50 Unsealed Terminals [560023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[206523-2162](#)