

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5023801000**  
**Status:** **Active**  
**Overview:** CLIK-Mate Wire-to-Board Connectors  
**Description:** 1.25mm Pitch CLIK-Mate Wire-to-Board Housing, Single Row, Positive Lock, 10 Circuits, White

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-502380-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Application Specification AS-502380-002-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification SPK-502380-001-001 (PDF)</a>
<a href="#">Product Specification PS-502382-001-001 (PDF)</a>	<a href="#">Packaging Specification SPK-502380-001-002 (PDF)</a>
<a href="#">Product Specification PS-502382-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<u>502380</u>
Application	Signal, Wire-to-Board
Overview	<u>CLIK-Mate Wire-to-Board Connectors</u>
Product Name	CLIK-Mate
UPC	822350895125

**Physical**

Breakaway	No
Circuits (maximum)	10
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	257.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Electrical**

Current - Maximum per Contact	1.0A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-502380-001-001, AS-502380-002-001
Packaging Specification	SPK-502380-001-001, SPK-502380-001-002
Product Specification	PS-502382-001-001, PS-502382-002-001
Sales Drawing	SD-502380-001-001, SD-502380-001-002, SD-502380-002-001, SD-502380-002-002



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

502380 Series

**Mates With**

CLIK-Mate PCB Receptacle 502382 ,  
502386

**Use With**

CLIK-Mate Terminal 502381 <br> CLIK-Mate Pre-Crimped Leads 797581012 ,  
797581013

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[502380-1000](#)