

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934441101](#)
Status: **Active**
Overview: [ML-XT Sealed Connection System](#)
Description: ML-XT Sealed 2 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

3D Model	Application Specification 934430010-A (PDF)
3D Model (PDF)	Packaging Specification 934430002-K (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 934430010-P (PDF)	Product Literature (PDF)
Product Specification STR-1707-001 (PDF)	

Agency Certification

UL E29179

Application tooling part link

Application Tooling Part Link 63824-5300

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT Sealed Connection System
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	887191604220

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.807/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C

Electrical

Current - Maximum per Contact 13.0A

Material Info

Reference - Drawing Numbers

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P, STR-1707-001
Sales Drawing	934430010-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93444 Series](#)

Mates With

ML-XT Sealed 2 Circuit Plug Housing [934451101](#)

Use With

ML-XT Male (Pin) Terminal [845240004](#) (Nickel), ML-XT Male (Pin) Terminal [845240014](#) (Selective Gold), ML-XT 2 Circuit Receptacle Wedglock [93447](#) , ML-XT Blind Cavity Plug [934941000](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for ML-XT Sealed	638245300
----------------------------------	---------------------------

This document was generated on 11/05/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93444-1101](#)