

F

E

D

C

B

A

F

E

D

C

B

A

ENG NO:		AE-3190-NA-*			
DIM "D"		(11.43) .450			
DIM "C"		(19.05) .750			
NO. OF CKTS	VOID LOCATION	PART NO.	ENG NO.	DIM. "A"	DIM. "B"
3	3	38-00-7587	AE-3190-3A-51	(7.92 ±0.25) .312 ±.010	(11.89) .486
4	2	↑ -7260	↑ -4A-51	(11.89) .469	(15.85) .624
4	3	-7261	-4A-52	(11.89) .469	(15.85) .624
5	2	-7588	-5A-54	(15.85) .624	(19.81) .780
5	3	-1589	-5A-03	(15.85) .624	(19.81) .780
5	4	-7604	-5A-04	(15.85) .624	(19.81) .780
5	2&4	-1200	-5A-51	(15.85) .624	(19.81) .780
5	1,3	-7262	-5A-52	(15.85) .624	(19.81) .780
5	3,5	-1588	-5A-53	(15.85) .624	(19.81) .780
6	3	-7642	-6A-54	(19.81) .780	(23.77) .936
6	4	-7263	-6A-51	(19.81) .780	(23.77) .936
6	5	-7641	-6A-53	(19.81) .780	(23.77) .936
6	3,6	-7589	-6A-52	(19.81) .780	(23.77) .936
7	6	-7605	-7A-06	(23.77) .936	(27.74) 1.092
8	4	-7590	-8A-51	(27.74) 1.092	(31.70) 1.248
9	4,7	-7638	-9A-52	(31.70) 1.248	(35.66) 1.404
10	3,4	-7639	-10A-51	(35.66) 1.404	(39.62) 1.560
11	6	-7591	-11A-55	(39.62) 1.560	(43.59) 1.716
11	2,4,8	-7264	-11A-52	(39.62) 1.560	(43.59) 1.716
11	3,4,8	-1587	-11A-53	(39.62) 1.560	(43.59) 1.716
11	4,8,9	-1586	-11A-54	(39.62) 1.560	(43.59) 1.716
13	3	-7669	-13A-3	(47.55) 1.872	(51.51) 2.028
13	4,8,11	-7640	-13A-51	(47.55) 1.872	(51.51) 2.028
15	3,9	↓ -8241	↓ -15A-52	(55.47) 2.184	(59.44) 2.340
15	9,13	38-00-8242	AE-3190-15A-53	(55.47±0.25) 2.184±.010	(59.44) 2.340

OBSOLETE PART #S

EC NO: UCP2011-0768

DRWN:KIPPER 2010/09/20

CHKD:SSOUSEK

APPR:FSM TH 2011/02/11

REV

AC

QUALITY SYMBOLS

F_A=0

F_C=0

F_P=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± ---

2 PLACES ± --- ± ---

1 PLACE ± --- ± ---

ANGULAR ± ---°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM/IN

DRAWN BY

DATE

M.GOONEY 2000/10/23

CHECKED BY

DATE

E.FOLAN 2000/11/09

APPROVED BY

DATE

M.WILHITE 2000/11/09

MATERIAL NO.

SEE CHART

SCALE

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

WAFER POLARIZING KK .156 (3.96)/.156,MOLDED FOR (1.14)/.045RD,PIN,W/VOID

MOLEX INCORPORATED

DOCUMENT NO.

SHEET NO.

SDAE-3190-N** 2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

9

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[38-00-8242](#)