

2.4 GHz External Whip Antenna

AEACAC049009-S2400

Request Samples



Check Inventory



49.3 x Ø9.2 mm

RoHS/RoHS II Compliant

MSL Level = 1

Features

- Small Form Factor
- Cable + Connector Options
- VSWR $\leq$ 2.0
- Gain of 2dBi

Applications

- WiFi/Bluetooth/ZigBee
- ISM Applications
- Wireless Communication System
- Network Devices
- Set top Boxes

Electrical Specifications

Parameter	Specification			Unit
	Min	Typ	Max	
Operating Frequency	2400		2483.5	MHz
Bandwidth		83.5		MHz
VSWR			2.0	
Gain		2.0		dBi
Impedance	50			Ω
Polarization	Linear			

Mechanical Specifications

Parameter	Specification
Antenna Dimension	49.3 x Ø9.2 mm
Connector Type	IPEX-1 (Female)
Cable Type	RG178
Cable Length	100 mm

2.4 GHz External Whip Antenna

AEACAC049009-S2400

Request Samples



Check Inventory




49.3 x Ø9.2 mm
RoHS/RoHS II Compliant
MSL Level = 1


Environmental Specification

Parameter	Specification
Operating Temperature	-40 °C to +85 °C
RoHS Compliance	Yes
PB Free	Yes
MSL	1
ESD Sensitive	No
Vibration	10 ~ 55 Hz with 1.5 mm amplitude 2 hrs

Product Image & Dimension



Unit : mm



2.4 GHz External Whip Antenna

AEACAC049009-S2400

Request Samples



Check Inventory





49.3 x Ø9.2 mm

RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics



Packaging Information

Number of Antenna/ Carton : 1000

Dimension of the Carton : 370 x 360 x 170 mm

Weight of the Carton: 9Kgs

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 02-18-20

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AEACAC049009-S2400](#)