










		Example Part Number ⁱ	Size Range	Options	Description ⁱⁱ	Selling Tips
	Pan-Wrap™ Split Harness Wrap	PW50F-T PW50FR-TY	.38" to 1.63" capacity	<ul style="list-style-type: none"> Material Colors Sizes 	Provides improved flexibility and abrasion protection in any application. Provides for easy wire or cable breakouts. Maintains uniform bundle protection in dynamic applications	<ul style="list-style-type: none"> Patented slot pattern The patented installation tool allows easy loading of maximum bundle diameters to speed installation considerably by simply pulling the tool along the bundle length Large overlap Natural and Flame Retardant Polyethylene Material
	Spiral Wrap	T12F-C T12F-C0 T12R-CY T12FR-CY T12N-C	1/16" to 6" capacity	<ul style="list-style-type: none"> Material Colors Sizes 	Spiral Wrap offers abrasion protection for wires, cables, hoses and tubing	<ul style="list-style-type: none"> Contractor Grade Cut to Length Continuous temperature range 12 colors to allow color coding Available in high temp UV weather resistant for alternative energy (wind, solar) Chemical resistant materials available
	Grommet Edging	GEE36F-C GEE36F-C0 GEE36FR-CY GEE47N-C	.026" to .510" capacity	<ul style="list-style-type: none"> Material Slotted/Solid 2 Colors Sizes 	Protects and insulates wires and cables from chafing against sharp edges. Use product on irregularly shaped and round panel holes.	<ul style="list-style-type: none"> Standard Grommet Edging and Adhesive Lined Application includes install on panels
	Corrugated Loom Tubing - Slit	CLT25F-C3 CLT25N-C630	.27" to 1.88" capacity	<ul style="list-style-type: none"> Material Slit Wall/Solid Wall Sizes Colors 	Slit Corrugated Loom Tubing is offered for applications where Spiral Wrap or Braided Expandable Sleeving may be difficult to install or they do not offer the amount of protection required.	<ul style="list-style-type: none"> Slit allows for easy installation of cable bundle Packaged on a reel for easy handling and dispensing of product
	Braided Expandable Sleeving	SE12P-TR0 SE12PFR-TR0	.094" to 2.75" capacity	<ul style="list-style-type: none"> Material Standard/Fray Resistant Colors Sizes 	Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.	<ul style="list-style-type: none"> Lightweight, durable protection Highly flexible open weave will not trap heat or humidity Rated for use up to 257°F (125°C) Compliant with U.S. and European passenger rail standards

	Example Part Number ⁱ	Size Range	Options	Description ⁱⁱ	Selling Tips
	TV105-12MY	.089" to 1.036 capacity	<ul style="list-style-type: none"> • Black/Clear • Sizes 	Provides insulation and protection for lead wires, wire harness assemblies, soldered joints and components in electrical and electronic equipment. All purpose flexible non-shrinkable. Resistant to heat and moisture	<ul style="list-style-type: none"> • Material: Polyvinyl chloride (PVC) • Voltage Rating: 300V and 600V • All purpose flexible non-shrinkable • Resistant to heat and moisture
	HSTT06-C HSTTA19-Y HST0.4-48-5Y		<ul style="list-style-type: none"> • Dry, Damp and Wet Shrink • Materials • Sizes • Colors 	Used to insulate and protect oversized electrical and electronic components, cables, terminals and connectors in a wide variety of applications.	<ul style="list-style-type: none"> • Available for multiple applications and markets • Can be used for color coding • Voltage Rating: up to 600V • Shrink Ratios - 2:1, 2.5:1, 3:1 or 4:1 • HST: UL approved for outdoor use in alternative energy applications (wind, solar)

Accessories:

 <p>Pan-Wrap Installation Tool</p>	 <p>Corrugated Loom Tubing Fittings</p>	 <p>Expandable Sleeving Tooling Head</p>	 <p>Heat Shrink Tools and Accessories</p>
--	---	--	--

Certifications, Markings, Compliances ⁱⁱⁱ :			RoHS
Products:	Pan-Wrap, Spiral Wrap, Braided Sleeving, Non-Shrink PVC Tubing, Heat Shrink Tubing*, Grommet Edging*	Braided Sleeving, Non-Shrink PVC Tubing, Heat Shrink Tubing*	All abrasion protection products

ⁱ For full part listing see www.panduit.com for online catalog, or reference printed catalogs.

ⁱⁱ Color availability varies among styles and certain colors may have limited sizes available

*Please see catalog for select materials

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[HST0.4-48-5Y](#)