

**® Cable Tie Mounts**



- Unique cradle design provides maximum stability for the cable bundle
- Low profile design keeps bundle close to mounting surface
- Material: Nylon 6.6 or as specified below

Part Number	Used With Cable Ties	Length		Width		Height		Color	Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	In.	mm				
TM1S4-C	M	.51	13.0	.32	8.0	.23	5.8	Natural	#4 (M2.5) screw	100	500
TM1S4-C0*	M							Black		100	500
TM1S6-C	M							Natural	#6 (M3) screw	100	500
TM1S6-C0*	M							Black		100	500
TM2S6-C	M, I, S	Natural	#8 (M4) screw	100	500						
TM2S6-C0*	M, I, S	Black		100	500						
TM2S8-C	M, I, S	Natural		#10 (M5) screw	100	500					
TM2S8-C0*	M, I, S	Black			100	500					
TM3S8-C	M, I, S, LH	Natural	#10 (M5) screw		100	500					
TM3S8-C0*	M, I, S, LH	Black			100	500					
TM3S10-C	M, I, S, LH	Natural		1/4" (M6) screw	100	500					
TM3S10-C0*	M, I, S, LH	Black			100	500					
TM3S2510-C30**	M, I, S, LH	Black	100		500						
TM3S2510-C39**	M, I, S, LH	Natural	100		500						
TM3S25-C	M, I, S, LH	.88	22.3	.63	16.0	.38	9.6	Natural	100	500	
TM3S25-C0*	M, I, S, LH	.88	22.3	.63	16.0	.38	9.6	Black	100	500	

\*Material: Weather Resistant Nylon 6.6

\*\*Material: Heat Stabilized Nylon 6.6

Cable Tie Cross Sections: M = Miniature, I = Intermediate, S = Standard, LH = Light-Heavy.

**® Extra-Heavy Cable Tie Mounts**

- Unique cradle design provides maximum stability for cable bundle
- Route and support large diameter and heavy cable bundles
- Dimensions are 1.62"L x 0.72"W x .61"H (41.4mm x 18.8mm x 15.5mm)\*
- Weather resistant material for indoor/outdoor use



Part Number	Used With Cable Ties	Material	Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
TMEH-S8-Q0	I, S, H, EH	Weather Resistant Nylon 6.6	#8 (M4) Screw	25	250
TMEH-S10-Q0			#10 (M5) Screw	25	250
TMEH-S10-C100		Weather Resistant Polypropylene	#10 (M5) Screw	100	500
TMEH-S10-C109		Polypropylene	#10 (M5) Screw	100	500
TMEH-S25-Q0		Weather Resistant Nylon 6.6	1/4" (M6) Screw	25	250

All product color is black.

\*Polypropylene parts (TMEH-S10-C100, TMEH-S10-C109) have an overall length of 1.65" (41.9mm).

Cable Tie Cross Sections: I = Intermediate, S = Standard, H = Heavy, EH = Extra Heavy.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[TM3S10-C0](#)