



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DESCRIPTION	DIM "A"	DIM "B"	WEIGHT
XG-DRSP642*	600X42RU FLEXFUSION SPLIT DOOR	583.8 [22.98]	1949.2 [76.74]	10.2 Kg/EACH 22.4 LBS/EACH
XG-DRSP645*	600X45RU FLEXFUSION SPLIT DOOR		2082.6 [81.99]	10.9 Kg/EACH 24.0 LBS/EACH
XG-DRSP648*	600X48RU FLEXFUSION SPLIT DOOR		2215.9 [87.24]	11.5 Kg/EACH 25.3 LBS/EACH
XG-DRSP651*	600X51RU FLEXFUSION SPLIT DOOR		2349.3 [92.49]	12.0 Kg/EACH 26.5 LBS/EACH
XG-DRSP742*	700X42RU FLEXFUSION SPLIT DOOR	683.8 [26.92]	1949.2 [76.74]	10.9 Kg/EACH 24.0 LBS/EACH
XG-DRSP745*	700X45RU FLEXFUSION SPLIT DOOR		2082.6 [81.99]	11.5 Kg/EACH 25.4 LBS/EACH
XG-DRSP748*	700X48RU FLEXFUSION SPLIT DOOR		2215.9 [87.24]	12.1 Kg/EACH 26.7 LBS/EACH
XG-DRSP751*	700X51RU FLEXFUSION SPLIT DOOR		2349.3 [92.49]	12.7 Kg/EACH 28.0 LBS/EACH
XG-DRSP842*	800X42RU FLEXFUSION SPLIT DOOR	783.8 [30.86]	1949.2 [76.74]	11.2 Kg/EACH 24.7 LBS/EACH
XG-DRSP845*	800X45RU FLEXFUSION SPLIT DOOR		2082.6 [81.99]	11.8 Kg/EACH 26.0 LBS/EACH
XG-DRSP848*	800X48RU FLEXFUSION SPLIT DOOR		2215.9 [87.24]	12.4 Kg/EACH 27.4 LBS/EACH
XG-DRSP851*	800X51RU FLEXFUSION SPLIT DOOR		2349.3 [92.49]	13.0 Kg/EACH 28.7 LBS/EACH

* DENOTES COLOR
ADD SUFFIX "B" FOR BLACK AND "W" FOR WHITE.

						TITLE FLEXFUSION SPLIT DOOR (XG-DRSP6***, XG-DRSP7*** & XG-DRSP8***)						
						CUSTOMER DRAWING						
						ITEM REVISION NAME 00461EZB/00		PANDUIT				
						DATASET FILE NAME 00461EZB_DC/00A						
								MATERIAL: N/A				
00A	2/12/21	MEX-JAGC	MCIS	MCIS	DRAWING RELEASE	V09002EP/07		DRAWING NUMBER: 00461EZB_DC				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MEX-JAGC	DATE 2/12/21	CHK MCIS	SCALE NONE	SHT 2 OF 2	SIZE A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[XG-DRSP645W](#) [XG-DRSP642W](#) [XG-DRSP751B](#) [XG-DRSP651W](#) [XG-DRSP851B](#) [XG-DRSP748B](#) [XG-DRSP648B](#)
[XG-DRSP745W](#) [XG-DRSP845B](#) [XG-DRSP848B](#) [XG-DRSP651B](#) [XG-DRSP742B](#) [XG-DRSP851W](#) [XG-DRSP742W](#)
[XG-DRSP845W](#) [XG-DRSP848W](#) [XG-DRSP745B](#) [XG-DRSP642B](#) [XG-DRSP751W](#) [XG-DRSP648W](#) [XG-](#)
[DRSP645B](#) [XG-DRSP748W](#) [XG-DRSP842B](#) [XG-DRSP842W](#)