




Mini-Com® Classic Series Faceplates

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Optional adhesive labels available



CFP1IW CFP2IW CFP4IW



CFPH2IW CFPH4IW

Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFP1IW	Single gang, vertical faceplate accepts one Mini-Com® Module.	Off White	1	10
CFP2IW	Single gang, vertical faceplate accepts two Mini-Com® Modules.	Off White	1	10
CFP4IW	Single gang, vertical faceplate accepts four Mini-Com® Modules.	Off White	1	10
CFPH2IW	Single gang, horizontal faceplate accepts two Mini-Com® Modules.	Off White	1	10
CFPH4IW	Single gang, horizontal faceplate accepts four Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), or IG (International Gray). All faceplates supplied with mounting screws.

Component Labels for Mini-Com® Classic Series Faceplates



Suggested Label Solutions for TIA/EIA-606-A Compliance

Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CFP1	C061X030FJJ	C061X030YPT	C061X030FJC	T031X000FJC-BK
CFP2	C125X030FJJ	C125X030YPT	C125X030FJC	T031X000FJC-BK
CFP4				
CFPH2	C252X030FJJ	C252X030YPT	C252X030FJC	T031X000FJC-BK
CFPH4				

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.



Mini-Com® Classic Series Faceplate Kits

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Inserts are front releasable
- Optional adhesive labels available



CFPS4IW CFPP12IW-2G

Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFPS4IW	Single gang, vertical faceplate frame and two sloped inserts (two module spaces each). Accepts four Mini-Com® Modules.	Off White	1	10
CFPP12IW-2G	Double gang, vertical faceplate frame and six flat inserts (two module spaces each). Accepts twelve Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), or IG (International Gray). All faceplates supplied with mounting screws.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CFPF12IW-2G](#) [CFPS4IW](#) [CFPH4IW](#) [CFPH2IW](#)