



# GMSTBA 2,5 HC/ 5-G-7,62 GY7035 - 1705764

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB headers, nominal current: 16 A, number of positions: 2, pitch: 7.62 mm, color: light gray, contact surface: Tin, mounting: Wave soldering



## Key Commercial Data

Packing unit	50 pc
GTIN	 4 046356 796811
GTIN	4046356796811

## Technical data

### Dimensions

Length [ l ]	12 mm
Width	38.1 mm
Pitch	7.62 mm
Dimension a	30.48 mm
Width [ w ]	38.1 mm
Height [ h ]	12.1 mm
Height	8.6 mm
Length of the solder pin	3.5 mm
Length	12 mm

### General

Range of articles	GMSTBA 2,5 HC/...G
Rated voltage (III/3)	500 V
Connection in acc. with standard	EN-VDE
Nominal current I <sub>N</sub>	16 A
Color	light gray
Number of positions	2

### Standards and Regulations

Connection in acc. with standard	EN-VDE
----------------------------------	--------

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

# GMSTBA 2,5 HC/ 5-G-7,62 GY7035 - 1705764

## Technical data

### Environmental Product Compliance

	No hazardous substances above threshold values
--	--

## Approvals

### Approvals

#### Approvals

EAC / cULus Recognized

#### Ex Approvals

### Approval details

EAC		B.01742
-----	--	---------

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E60425-19931013
------------------	--	---

	D	B
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	20 A

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1705764](#)