

Marker carriers - UBE - 0800310


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Terminal strip marker carriers for marking terminal groups, for end bracket E/UK or end clamp E/U, lettering field size: 40 x 17 mm



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 005917
GTIN	4017918005917

Technical data

Dimensions

Length (b)	41.4 mm
Width (a)	20 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	gray
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Marking mounting type	plug in

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

Marker carriers - UBE - 0800310

Technical data

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27144075
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27149153
eCl@ss 9.0	27144075

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC002248
ETIM 7.0	EC002248

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 19.0	39131505

Accessories

Accessories

Conductor marking

Insert label - EMT (40X17)R - 0817293



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 16 ... 35 mm, lettering field size: 40 x 17 mm, Number of individual labels: 2300

Marker carriers - UBE - 0800310

Accessories

Terminal marking

Insert strip - ESL 40X17 - 0808095



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, perforated, mounting type: insert, lettering field size: 40 x 17 mm, Number of individual labels: 56

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0800310](#)