

Cable marker carrier - LM - 1004377

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter range: 1 ... 12 mm, lettering field size: 24 x 4 mm

Your advantages

- An insert label is placed inside the sealing cap to protect the labeling against dirt
- Plastic cable markers for marking and bundling conductors and cables indoors

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 012069
GTIN	4017918012069

Technical data

Dimensions

Length (b)	24 mm
Width (a)	4 mm
Cable diameter	1 mm ... 12 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	white
Type	Mounting set
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Marking mounting type	Assembly with cable binders

Cable marker carrier - LM - 1004377

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Conductor marking

Cable marker carrier - LM - 1004377

Accessories

Insert label - EMT (24X4)R - 0816265



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter: ≤ 12 mm, lettering field size: 24 x 4 mm, Number of individual labels: 5000

Terminal marking

Insert strip - ESL 24X4 - 0808231



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Perforated and ruled, mounting type: insert, lettering field size: 24 x 4 mm, Number of individual labels: 488

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1004377](#)