

DIN rail perforated - NS 35/15 WH PERF(5,2X25)2000MM - 1206476

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, Hole size: 5.2 x 25 mm, color: silver

Key Commercial Data

| | |
|--------------|---------------|
| Packing unit | 5 pc |
| GTIN | |
| GTIN | 4017918170899 |

Technical data

Dimensions

| | |
|--------------------|----------|
| Height | 15 mm |
| Length | 2000 mm |
| Width | 35 mm |
| Hole width | 25.00 mm |
| Hole height | 5.20 mm |
| Drill hole spacing | 36.00 mm |

General

| | |
|----------|------------------------------|
| Material | Steel |
| Coating | Galvanized, white passivated |
| Color | silver |

Standards and Regulations

| | |
|----------------------------------|---------------------|
| Test standard | similar to EN 60715 |
| Connection in acc. with standard | IEC / EN |

DIN rail perforated - NS 35/15 WH PERF(5,2X25)2000MM - 1206476

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400602 |
| eCl@ss 4.0 | 27110800 |
| eCl@ss 4.1 | 27110800 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27400600 |
| eCl@ss 7.0 | 27400602 |
| eCl@ss 8.0 | 27400602 |
| eCl@ss 9.0 | 27400602 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001285 |
| ETIM 3.0 | EC001285 |
| ETIM 4.0 | EC000212 |
| ETIM 5.0 | EC000212 |
| ETIM 6.0 | EC001285 |
| ETIM 7.0 | EC001285 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11 | 39121708 |
| UNSPSC 12.01 | 39121708 |
| UNSPSC 13.2 | 39121708 |
| UNSPSC 18.0 | 39121708 |
| UNSPSC 19.0 | 39121708 |
| UNSPSC 20.0 | 39121708 |
| UNSPSC 21.0 | 39121708 |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1206476](#)