

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Your advantages

- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections
- Unlockable pressure lock



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 453837
GTIN	4046356453837

Technical data

Dimensions

Length (b)	198 mm
Width (a)	18 mm
Height (c)	59 mm

General

Color	black
Compression	B crimp
Type of contact	Slip-on sleeve
Designation	Crimping position 1
Min. cross section	0.1 mm ²
Max. cross section	0.5 mm ²
AWG min	26
AWG max	22
Designation	Crimping position 2
Min. cross section	0.5 mm ²
Max. cross section	1 mm ²

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048

Technical data

General

AWG min	22
AWG max	18
Designation	Crimping position 3
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	18
AWG max	16
Die station	Crimping position 4
	Crimping position 5
Weight	350 g
Min. cross section	0.1 mm ²
Max. cross section	1.5 mm ²
AWG min	26
AWG max	16

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Drawings

Product drawing

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048

Classifications

eCl@ss

eCl@ss 9.0	21043811
------------	----------

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Accessories

Accessories

Die

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048

Accessories

Replacement die - CRIMPFOX-SC 1,5/DIE - 1212049



Spare die for CRIMPFOX-SC 1,5

Mounting material

Replacement spring - CRIMPFOX/ SPR-3 - 1212036



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212048](#)