

Conversion kit - CF 3000-TOOLKIT 0,25 - 1212376

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Extension kit, complete, for CF 3000, for taped insulated ferrules, 0.25/0.34 mm², sleeve length 8 mm

Your advantages

- ✔ Suitable for class 2 and class 5 PVC conductors (H05V-K/H07V-K).
Conductors with special insulating material and stranding can only be processed to a limited degree and with reservations.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 461467
GTIN	4046356461467

Technical data

General

Compression	Trapezoidal crimp
Type of contact	Ferrules
Min. AWG, flexible, multi-strand	22
AWG max., flexible, multi-strand	24
Conductor type	PVC
Min. cross section	0.25 mm ²
Max. cross section	0.34 mm ²
AWG min	24
AWG max	22

Classifications

eCl@ss

eCl@ss 10.0.1	17139201
---------------	----------

Conversion kit - CF 3000-TOOLKIT 0,25 - 1212376

Classifications

eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	17139201

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Conversion kit - CF 3000-TOOLKIT 0,25 - 1212376

Approvals

EAC



RU C-
DE.AI30.B.01549

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212376](#)