

Diagonal cutter - MICROFOX-SB - 1212489

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Your advantages

- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- Opening spring for uniform, smooth opening
- Through-connected joint for permanent stability and optimum distribution of force
- Made from special high-grade tool steel
- Mirror-polished and oiled metal surfaces, which provide maximum rust protection
- For a variety of applications

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 527200
GTIN	4046356527200

Technical data

Dimensions

Length (b)	115 mm
------------	--------

General

Weight	80 g
--------	------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043711
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300

Diagonal cutter - MICROFOX-SB - 1212489

Classifications

eCl@ss

eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043711
eCl@ss 8.0	21043711
eCl@ss 9.0	21043711

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000165
ETIM 5.0	EC000165
ETIM 6.0	EC000165
ETIM 7.0	EC000165

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111511
UNSPSC 18.0	27111511
UNSPSC 19.0	27111511
UNSPSC 20.0	27111511
UNSPSC 21.0	27111511

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212489](#)