

# Torque screwdriver - TSD 08 SAC - 1212597

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Torque screw driver with preset torque of 0.8 Nm, with 4 mm hexagon for accommodating SAC bits, two-component handle with non-slip grip

The figure shows the TSD 04 SAC version

## Your advantages

- ✓ Wide range of SAC... nuts for various different applications
- ✓ For the TSD-M... torque screwdrivers, the torque can be custom-set
- ✓ TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm
- ✓ The TSD-M... adapters can accommodate the various nuts

## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 590716
GTIN	4046356590716

## Technical data

### Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade thickness	0 mm
Blade width	0 mm
Blade height	100 mm

### General

Color	black
Type	Hexagonal SW4
Material	alloyed tool steel

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

# Torque screwdriver - TSD 08 SAC - 1212597

## Classifications

### eCl@ss

eCl@ss 10.0.1	21040417
eCl@ss 4.0	21040200
eCl@ss 4.1	21040200
eCl@ss 5.0	21040200
eCl@ss 5.1	21040200
eCl@ss 6.0	21040200
eCl@ss 7.0	21040417
eCl@ss 8.0	21040417
eCl@ss 9.0	21040417

### ETIM

ETIM 4.0	EC000149
ETIM 5.0	EC002132
ETIM 6.0	EC002132
ETIM 7.0	EC002132

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## Approvals

### Approvals

---

#### Approvals

#### EAC

---

#### Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

## Accessories

### Accessories

## Torque screwdriver - TSD 08 SAC - 1212597

### Accessories

#### Screwdriver tools

Tool - SAC BIT QUICKON-W13 - 1212033



Nut for assembling pressure nuts with 13 mm wrench size, for 4 mm hexagonal drive

---

Tool - SACC BIT M12-D20 - 1208445



Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive

---

Tool - SAC BIT MIN-D25 - 1212512



Nut for assembling 7/8" connectors with a knurl diameter of 25 mm, with 4 mm hexagonal drive

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212597](#)