

Marker carriers - PAB-SK 30 - 1013290

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Marker carriers, transparent, unlabeled, mounting type: adhesive, lettering field size: 30 x 4 mm

Your advantages

- ✔ These carrier materials can be fitted, e.g., with UC-WMT ... and EMT ...
- ✔ Powerful adhesion and optimum grip on standard device surfaces
- ✔ Self-adhesive marker carriers for marking devices and components

RoHS

Key Commercial Data

Packing unit	200 pc
Minimum order quantity	200 pc
GTIN	 4 017918 013707
GTIN	4017918013707

Technical data

Dimensions

Length (b)	30 mm
Width (a)	9 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
---------------------------------	------------------

General

Color	transparent
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
Marking mounting type	adhesive

Standards and Regulations

Marker carriers - PAB-SK 30 - 1013290

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 10.0.1	27144075
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27141137
eCl@ss 9.0	27144075

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC002248
ETIM 7.0	EC002248

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 19.0	39131504

Accessories

Accessories

Conductor marking

Cable marker - UC-WMT (30X4) - 0819437



Cable marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Marker carriers - PAB-SK 30 - 1013290

Accessories

Cable marker - UC-WMT (30X4) YE - 0819440



Cable marker, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) BU - 0821153



Cable marker, Sheet, blue, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) RD - 0821166



Cable marker, Sheet, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) OG - 0824150



Cable marker, Sheet, orange, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) GN - 0824163



Cable marker, Sheet, green, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Marker carriers - PAB-SK 30 - 1013290

Accessories

Cable marker - UC-WMT (30X4) VT - 0825364



Cable marker, Sheet, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Labeled conductor marker

Cable marker - UC-WMT (30X4) CUS - 0824848



Cable marker, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) YE CUS - 0824849



Cable marker, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) BU CUS - 0824852



Cable marker, can be ordered: by sheet, blue, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) RD CUS - 0824855



Cable marker, can be ordered: by sheet, red, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Marker carriers - PAB-SK 30 - 1013290

Accessories

Cable marker - UC-WMT (30X4) OG CUS - 0824854



Cable marker, can be ordered: by sheet, orange, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) GN CUS - 0824853



Cable marker, can be ordered: by sheet, green, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Cable marker - UC-WMT (30X4) VT CUS - 0826797



Cable marker, can be ordered: by sheet, violet, labeled according to customer specifications, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 16

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1013290](#)