

Crimping pliers - CRIMPFOX 50R CUS - 1212766

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 35 mm² ... 50 mm², lateral entry, WM crimp


The figure shows CRIMPFOX-RCI 6 CUS

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 942935
GTIN	4046356942935

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height (c)	68 mm

General

Compression	WM crimp
Type of contact	Ferrules
Weight	578 g
Min. cross section	35 mm²
Max. cross section	50 mm²
AWG min	2
AWG max	1

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

Crimping pliers - CRIMPFOX 50R CUS - 1212766

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Crimping pliers - CRIMPFOX 50R CUS - 1212766

Accessories

Accessories

Die

Replacement die - CRIMPFOX 50R/DIE - 1212042



Spare die, for CRIMPFOX 50R

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212766](#)