

## Torque screwdriver - TSD 04 SAC - 1208429

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

### Your advantages

- ✔ Wide range of SAC... nuts for various different applications
- ✔ TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm
- ✔ For the TSD-M... torque screwdrivers, the torque can be custom-set
- ✔ The TSD-M... adapters can accommodate the various nuts

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 014519
GTIN	4046356014519

### Technical data

#### Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade thickness	0 mm
Blade width	0 mm
Blade height	100 mm

#### General

Color	black
Type	Hexagonal SW4

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

# Torque screwdriver - TSD 04 SAC - 1208429

## Classifications

### eCl@ss

eCl@ss 10.0.1	21040417
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21040417
eCl@ss 8.0	21040417
eCl@ss 9.0	21040417

### ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC002132
ETIM 6.0	EC002132
ETIM 7.0	EC002132

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## Approvals

### Approvals

Approvals

EAC

Ex Approvals

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

## Torque screwdriver - TSD 04 SAC - 1208429

### Accessories

#### Accessories

#### Screwdriver tools

##### Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a knurl diameter of 15 mm, for 4 mm hexagonal drive

---

##### Tool - SACC BIT M12-D20 - 1208445



Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive

---

##### Adapter - SAC BIT M12-W14 - 1212513



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a hexagonal knurl wrench size of 14 mm, with 4 mm hexagonal drive

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1208429](#)