

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Your advantages

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 453929
GTIN	4046356453929

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height (c)	68 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Technical data

General

AWG max	14
Designation	Crimping position 3
Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10
Weight	578 g
Min. cross section	0.5 mm ²
Max. cross section	6 mm ²
AWG min	20
AWG max	10

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Classifications

UNSPSC

UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Accessories

Accessories

Die

Replacement die - CRIMPFOX-RCI 6/DIE - 1212058



Spare die for CRIMPFOX-RCI 6

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212057](#)