

Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for coaxial connectors, 5.41 mm, 6.48 mm, 1.69 mm, HEX crimp

Your advantages

- Lateral conductor entry
- Unlockable pressure lock



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 453882
GTIN	4046356453882

Technical data

Dimensions

Length (b)	198 mm
Width (a)	18 mm
Height (c)	59 mm

General

Color	black
Compression	HEX crimp
Type of contact	Coaxial connectors
Designation	Crimping position 1
Crimping width	5.41 mm
Designation	Crimping position 2
Crimping width	6.48 mm
Designation	Crimping position 3
Crimping width	1.69 mm
Weight	350 g
Min. cross section	1.69 mm ²
Max. cross section	6.48 mm ²

Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

Technical data

Environmental Product Compliance


California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Drawings

Pictogram



Product drawing



Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Crimping pliers - CRIMPFOX-CX 6,48 - 1212095

Approvals

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Die

Replacement die - CRIMPFOX-CX 6,48/DIE - 1212286



Spare die for CRIMPFOX-CX 6,48

Mounting material

Replacement spring - CRIMPFOX/ SPR-3 - 1212036



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212095](#)