

Cable-cutting tool - CUTFOX 25 VDE - 1212127

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable cutter, precision blade with macro-notching, for copper and aluminum up to 70 mm², VDE 1000 V AC/1500 V DC tested

Your advantages

- VDE-tested cutting tools made from special high-grade tool steel
- Inductively hardened blades for long-term stable cutting performance

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356454261

Technical data

Dimensions

Length (b)	210 mm
------------	--------

General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746
Max. cross section	70 mm ²

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21044701
---------------	----------

Cable-cutting tool - CUTFOX 25 VDE - 1212127

Classifications

eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21049000
eCl@ss 7.0	21044701
eCl@ss 8.0	21044701
eCl@ss 9.0	21044701

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000142
ETIM 5.0	EC000142
ETIM 6.0	EC000142
ETIM 7.0	EC000142

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27111506
UNSPSC 18.0	27111506
UNSPSC 19.0	27111506
UNSPSC 20.0	27111506
UNSPSC 21.0	27111506

Approvals

Approvals

Approvals


VDE Zeichengenehmigung / EAC


Ex Approvals

Approval details

Cable-cutting tool - CUTFOX 25 VDE - 1212127

Approvals

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	109845
------------------------	---	---	--------

EAC			RU x- DE.xx08.B.02974
-----	---	--	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212127](#)