

Stripping tool - WIREFOX 6SC - 1212158

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Stripping tool, for cables and conductors (especially for cables protected against short circuits and ground leakages) 1.5 - 6 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade


Product Description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212152 WIREFOX 10/SB, direct replacement: 1212314 WIREFOX 6SC/SB

Your advantages

- ✓ Flexible, adjustable limit stop for the stripping length
- ✓ Practical integrated wire cutter
- ✓ WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 454438 |
| GTIN | 4046356454438 |

Technical data

Dimensions

| | |
|------------------|--------|
| Length (b) | 191 mm |
| Width (a) | 20 mm |
| Height (c) | 90 mm |
| Stripping length | 18 mm |

General

| | |
|--------------------|---------------------|
| Color | black/green |
| Weight | 136 g |
| Min. cross section | 1.5 mm ² |
| Max. cross section | 6 mm ² |
| AWG min | 16 |
| AWG max | 10 |

Environmental Product Compliance

Stripping tool - WIREFOX 6SC - 1212158

Technical data

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21043706 |
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043700 |
| eCl@ss 7.0 | 21043706 |
| eCl@ss 8.0 | 21043706 |
| eCl@ss 9.0 | 21043706 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC000163 |
| ETIM 5.0 | EC000163 |
| ETIM 6.0 | EC002109 |
| ETIM 7.0 | EC002109 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 27111518 |
| UNSPSC 18.0 | 27111510 |
| UNSPSC 19.0 | 27111510 |
| UNSPSC 20.0 | 27111510 |
| UNSPSC 21.0 | 27111510 |

Approvals

Approvals

Approvals

EAC

Stripping tool - WIREFOX 6SC - 1212158

Approvals

Ex Approvals

Approval details

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Knife

Spare knife - WIREFOX 6SC/SB - 1212314



Replacement blade for WIREFOX 6SC, for cables and conductors (especially for cables protected against short circuits and ground leakages) 1.5 - 6 mm²

Spare knife - WIREFOX 4/SB - 1212151



Replacement blade for WIREFOX 4, for cables and conductors (especially for rubber and silicone insulations) of 0.1 - 4 mm²

Spare knife - WIREFOX 10/SB - 1212152



Replacement blade for WIREFOX 10, for cables and conductors of 0.02 - 10 mm²

Spare knife - WIREFOX 16/SB - 1212153



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm²

Stripping tool - WIREFOX 6SC - 1212158

Accessories

Stripping tool

Replacement limit stop - WIREFOX 10/WS - 1200285

Replacement limit stop

Replacement retaining jaw - WIREFOX 10/CJ - 1200286

Replacement clamping jaws for WIREFOX 4, WIREFOX 6SC, and WIREFOX 10



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212158](#)