

Diagonal cutter - CUTFOX-SP VDE - 1212206

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power diagonal cutter, with optimized leverage, also suitable for piano wire, VDE 1000 V AC/1500 V DC tested

Your advantages

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 4 6 3 5 6 4 5 4 2 2 3
GTIN	4046356454223

Technical data

Dimensions

Length (b)	200 mm
Cable diameter	0.2 mm ... 4 mm

General

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746
Weight	315 g
Min. cross section	0 mm ²

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Diagonal cutter - CUTFOX-SP VDE - 1212206

Classifications

eCl@ss

eCl@ss 10.0.1	21043711
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043711
eCl@ss 8.0	21043711
eCl@ss 9.0	21043711

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000142
ETIM 5.0	EC000165
ETIM 6.0	EC000165
ETIM 7.0	EC000165

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27111511
UNSPSC 18.0	27111511
UNSPSC 19.0	27111511
UNSPSC 20.0	27111511
UNSPSC 21.0	27111511

Approvals

Approvals

Approvals


VDE Zeichengenehmigung / EAC

Ex Approvals

Approval details

Diagonal cutter - CUTFOX-SP VDE - 1212206

Approvals

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	109845
------------------------	---	---	--------

EAC			RU x- DE.xx08.B.02974
-----	---	--	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212206](#)