

Crimping pliers - CRIMPFOX-TC MP - 1212510

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

Your advantages

- Universal adjustment for precise processing of corresponding cross sections
- Crimping pliers for processing turned contacts of up to 2.5 mm²
- The integrated positioning tool ensures that the contacts are perfectly aligned



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356555500

Technical data

Dimensions

Length (b)	175 mm
------------	--------

General

Color	black
Compression	Four-mandrel crimping
Type of contact	Turned contacts
Weight	850 g
Min. cross section	0.08 mm ²
Max. cross section	2.5 mm ²
AWG min	28
AWG max	14

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Crimping pliers - CRIMPFOX-TC MP - 1212510


Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Drawings

Pictogram



Classifications

eCl@ss

eCl@ss 10.0.1	21043811
---------------	----------

Crimping pliers - CRIMPFOX-TC MP - 1212510

Classifications

eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Crimping pliers - CRIMPFOX-TC MP - 1212510

Approvals

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Crimping tool

Spare locator - CRIMPFOX-TC MP LOC - 1045123



Locator for CRIMPFOX-TC MP6

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212510](#)