

## Crimping pliers - CRIMPFOX 6S-F CUS - 1212769

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, front insertion, square crimp


The figure shows CRIMPFOX 6 CUS

### Your advantages

- ✓ Comprehensive range of crimping pliers
- ✓ All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- ✓ Consistently high crimping quality
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Unlockable pressure lock



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 942966
GTIN	4046356942966

### Technical data

#### Dimensions

Length (b)	198 mm
Width (a)	18 mm
Height (c)	59 mm

#### General

Color	black
Compression	Square crimp
Type of contact	Ferrules
Weight	376 g
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	20
AWG max	10

# Crimping pliers - CRIMPFOX 6S-F CUS - 1212769

## Technical data

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

## Drawings

Product drawing

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

### UNSPSC

UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Crimping pliers - CRIMPFOX 6S-F CUS - 1212769

### Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

### Accessories

Accessories

Mounting material

Replacement spring - CRIMPFOX/ SPR-3 - 1212036



Spare recuperating spring

---

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212769](#)