

## Crimping pliers - CRIMPFOX 16R TWIN - 1212845

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for TWIN ferrules according to UL 486F, three marked die stations, unlockable pressure lock, lateral entry

### Your advantages

- ✔ Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 406220
GTIN	4055626406220

### Technical data

#### Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height (c)	68 mm
Cable diameter	6 mm ... 8.5 mm

#### General

Color	black
Compression	WM crimp
Type of contact	TWIN ferrules
Max. cross section	6 mm <sup>2</sup>
	10 mm <sup>2</sup>
	16 mm <sup>2</sup>
Weight	578 g
Min. cross section	6 mm <sup>2</sup>
Max. cross section	16 mm <sup>2</sup>

### Environmental Product Compliance

# Crimping pliers - CRIMPFOX 16R TWIN - 1212845

## Technical data

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

## Crimping pliers - CRIMPFOX 16R TWIN - 1212845

### Approvals

Ex Approvals

---

#### Approval details

EAC



RU x-  
DE.xx08.B.02974

### Accessories

#### Accessories

##### Die

Replacement die - CRIMPFOX 16R TWIN/DIE - 1212846



Replacement die for CRIMPFOX 16R TWIN

---

#### Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212845](#)