

## DIN rail, unperforated - NS 15 BLK UNPERF 2000MM - 1401789

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, unperforated, Standard profile, width: 15 mm, height: 5.5 mm, acc. to EN 60715, material: Steel, uncoated, length: 2000 mm, color: white aluminum



### Key Commercial Data

Packing unit	5 pc
GTIN	
GTIN	4017918155421

### Technical data

#### Dimensions

Height	5.5 mm
Length	2000 mm
Width	15 mm
Hole width	0.00 mm
Hole height	0.00 mm
Drill hole spacing	0.00 mm

#### General

Material	Steel
Coating	uncoated
Color	white aluminum



#### Standards and Regulations

Test standard	acc. to EN 60715
Connection in acc. with standard	IEC / EN

### Drawings

## DIN rail, unperforated - NS 15 BLK UNPERF 2000MM - 1401789

Dimensional drawing



### Classifications

eCl@ss

eCl@ss 10.0.1	27400602
eCl@ss 4.0	27110800
eCl@ss 4.1	27110800
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

## DIN rail, unperforated - NS 15 BLK UNPERF 2000MM - 1401789

### Classifications

#### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 18.0	39121708
UNSPSC 19.0	39121708
UNSPSC 20.0	39121708
UNSPSC 21.0	39121708

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1401789](#)