

## Fuse - FUSE 10,3X38 15A PV - 3061348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

### Your advantages

- Use in PV lines with a nominal voltage of up to 1000 V DC

### Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 929448
GTIN	4046356929448

### Technical data

#### General

Color	white
-------	-------

#### Dimensions

Length	38 mm
Diameter	10.3 mm

#### General

Fuse	Midget / 10.3 x 38
Nominal voltage $U_N$	1000 V DC

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

# Fuse - FUSE 10,3X38 15A PV - 3061348

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 8.0	27142001
eCl@ss 9.0	27142001

### ETIM

ETIM 3.0	EC000035
ETIM 4.0	EC002704
ETIM 5.0	EC000035
ETIM 6.0	EC000035
ETIM 7.0	EC000035

### UNSPSC

UNSPSC 6.01	30211915
UNSPSC 7.0901	39121514
UNSPSC 11	39121514
UNSPSC 12.01	39121514
UNSPSC 13.2	39121629
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

## Approvals

### Approvals

---

Approvals

EAC

---

## Fuse - FUSE 10,3X38 15A PV - 3061348

### Approvals

Ex Approvals

---

#### Approval details

EAC



RU C-  
DE.BL08.B.00724

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3061348](#)