

Zack marker strip - ZB 10/VT CUS - 0824939

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack marker strip, can be ordered: Strip, violet, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 10.2 mm, lettering field size: 10.5 x 10.15 mm, Number of individual labels: 10



Key Commercial Data

| | |
|--------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356358927 |

Technical data

Dimensions

| | |
|-----------|-------|
| Width (a) | 10 mm |
|-----------|-------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

General

| | |
|--|--------------------------------|
| Color | violet |
| Type | high |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |
| Marking mounting type | snap into tall marker groove |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Zack marker strip - ZB 10/VT CUS - 0824939


Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V2 |
|--|----|

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

Zack marker strip - ZB 10/VT CUS - 0824939

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 9.0 | 27141137 |
|------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131505 |
| UNSPSC 18.0 | 39131505 |
| UNSPSC 19.0 | 39131505 |
| UNSPSC 20.0 | 39131505 |
| UNSPSC 21.0 | 39131505 |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0824939](#)